## **#smartconnection**



LANactive
Fibre To The Office

Catalogue



# Table of content

Make #smartconnections with Aginode	
Challenges with traditional LAN	4
Fibre To The Office - Simplify your network	!
Intelligent and robust switches	(
LANactive FTTO & DICE	{
LANactive Manager	9
Product overview	10
GigaSwitch V5 54V DC.     GigaSwitch V5 230V AC.     GigaSwitch V5 MED.	1
GigaSwitch V5 IND     Click-In Power Supplies     Installation Power Supplies	1
LANactive Manager	1 1
Aginode SFPs     Cover sets, Installation profile     Installation profile. Mounting Kit	1



# Make #smartconnections with Aginode.

Aginode, formerly Aginode Telecom Systems, designs & manufactures connectivity solutions for digital networks in FTTx, Mobile, LAN & Data Centre markets. Our goal: to enable the infrastructure which delivers applications that make lives more connected, productive, and enjoyable; today and in future. Our international teams have over 30 years proven track record of developing, implementing, and servicing advanced infrastructure solutions, with Aginode's diverse product range under our brand names:


- LAN & Data Centres: LANmark<sup>™</sup>, LANsense<sup>™</sup>, LANactive
- FTTx & Mobile: XPLORER™, BRIGHTBOX™, INFRABIRD™. UPSKY™

With a state-of-the-art industrial footprint and recognised technological know-how in Europe, Middle East, North-West Africa, and Asia, Aginode is a key player in digitalisation and connectivity.

# **Challenges with traditional LAN**

#### From complexity to flexibility

The number of applications running on networks keeps increasing each year. Server virtualisation, cloud computing, IP telephony, IPTV, security services, video conferencing and more require higher bandwidth, signal continuity and network scalability. IP convergence is also boosting the need for lasting infrastructures. However, when trying to keep up with today's network evolution and projected future developments, IT managers face several challenges.




# **Fibre To The Office**

#### Simplify your network

Aginode LANactive is an alternative LAN technology for use in office environments. Passive fibre cabling and active switches are combined to provide Gigabit Ethernet services from the central core switch to an FTTO switch and from there to end user devices. Although the entire network operates at 1 Gbps, throughput is as good as – or better than – that of a traditional network setup featuring floor distributors and an aggregated high-speed backbone. Performance is further supported by non-blocking switching and switches with 20 Gbps backplane.

LANactive switches ensure intelligent conversion from fibre to copper and vice versa. Each switch, installed at the workplace in cable ducts or floor boxes, is equipped with four copper RJ45 user ports to feed end user devices with data and power. Fibre speed, reliability and long distance coverage are coupled with the Ethernet benefits of copper. This solution meets current and foreseeable network requirements in terms of flexibility, cost efficiency and network interoperability. Regardless of their size and complexity, networks can be easily and cost-efficiently managed from a single location with the LANactive configuration and management platform from Aginode. Precise mapping of current infrastructure status makes it possible to track and repair faults or configuration errors fast, saving considerable time.

- · Easy and fast to install, adjust and repair
- Avoiding floor distributors to save space, costs and energy
- · Minimal cable volume and equipment footprint
- · Highly scalable and flexible
- Increased protection of investments



# Intelligent and robust switches

#### Easy to install

Compact, discreet FTTO switches are installed in cable ducts or floor boxes. Despite their small form factor, the switches offer up to four copper RJ45 user ports for delivering data and power to end user devices. As this is delivered over a relatively short distance – the last few metres of the network – there is less power loss and less energy required.

#### **Easy Configuration**

Optional memory cards with MAC addresses always store the latest full switch configuration automatically. If a switch needs to be replaced, all you need to do is remove the memory card and insert it into the new switch. No special knowledge or training required.

#### **Enhanced Energy Efficiency**


LANactive access switches are located close to the end user. These replace switches that would normally be located in a floor distribution room, which would require HVAC systems, lighting and so on. The FTTO switch itself consumes a minimum of power for data transmission. Switches also support Energy Efficient Ethernet (IEEE 802.3az), so that energy is only consumed when data is transferred. Aginode EcoMode optimises data transfer modes, based on current user needs and preferences.

#### **Data and Power**

The switch draws current from an external power supply, which can power all connected devices. As this is delivered over a relatively short distance – the last few metres of the network – there is less power loss and less energy is required.

#### Secure

Aginode switches provide the ideal basis for secure Local Area Networks. Intelligent Management and security features increase the security of the network and restrict unwanted data traffic in the access layer.







Aginode FTTO Switches are available with a rotatable head by default

#### Proven durability

LANactive solutions are based on selected industrial components, which are robust, durable and high-performing. Aginode carries out ongoing quality controls following the latest standards (ISO 9001). The result: an MTBF value (Mean Time Before Failure) of over 400 years.

#### Less space

LANactive FTTO doesn't require the bulky horizontal copper cable bundles generally used in traditional installations. This improves accessibility whilst reducing cabling volume by up to three-quarters. A considerable amount of room is saved in racks and cable pathways, adding up to considerable space savings on every floor. As fibre cabling requires no electrical grounding or shielding and is slimmer than copper conductors, it has a smaller overall cable diameter.

#### Longer distances

Fibre breaks through copper's 90-metre distance limit. Large distances, spanning hundreds of metres, between buildings, campuses and industrial sites can be easily bridged by fibre.

#### Flame retardant and fire retardant

Cabling used in an FTTO installation has outstanding flame retardant (IEC 60332-1) and fire retardant (IEC 60332-3) properties. Fibre cables comply with different fire performance classes and three additional criteria (smoke production, flaming droplets and acidity). These have been defined as part of the EU Construction Products Regulation (CPR) that now governs cable usage in buildings. In addition, the reduced cable volume and use of smaller bundles significantly reduces fire load, enhancing safety and making compliance with relevant regulations easier.

#### No interference


Fibre needs no grounding or earthing. Unlike copper, fibre is immune to electromagnetic interference and may run along power lines.

## **LANactive FTTO & DICE**

The XGigaSwitch DICE (Digital Ceiling) is an ideal extension of FTTO networks to provide more bandwidth and more power to the increasing number of connected devices in a Local Area Network. It provides more connectivity in places where it is needed – in the Digital Ceiling. Based on a future-proof fibre infrastructure only a minimum of cabling volume is necessary to connect the DICE switch. In combination with smart mounting options, the DICE switch can be used in multiple installation scenarios.


#### **Benefits**

- Scalable LAN infrastructure
- Future-proof technology
- Extended redundancy
- Fully automated with Zero-Touch Configuration
- · Space saving installation
- Savings in OPEX & CAPEX



# **LANactive Manager**

LANactive Manager provides an easy, comfortable and secure solution for configuration, management and supervision of Aginode LANactive switches.



All LANactive switches (FTTO, DICE and Industry) can be managed via LANactive Manager.

#### Accurate view with intelligent device lists

Categories can be defined according to a tree structure and devices can be assigned using Drag & Drop. Any number of device lists can be created, arranged in different groups, sorted by IP address, MAC address, device name and software version, or imported from environments such as XML, CSV or from a database. Counting and labelling according to category are also possible, along with various viewing options and creation of Excel or XML inventory lists. The device list is automatically updated through polling and changes are highlighted.

#### Software Packages

LANactive Manager is available as a standalone version and used as a desktop application for single or multiple users. This installation is perfect for on-site network engineers who are connected locally.

#### **LANactive Manager Client-Controller**

LANactive Manager Client-Controller is a client-controller software architecture that is optimised for large installations with hundreds or thousands of switches. It allows simultaneous access from different clients via client software or web interface and supports the fully automated configuration process Zero-Touch Configuration. The LANactive Manager Client-Controller is available for Windows and Linux operating systems.

#### **Zero-Touch Configuration**

Aginode LANactive Zero-Touch Configuration is a contemporary way of designing, building and operating networks with minimum effort. The use of LANactive Manager together with LANactive switches ensures networks are flexible and scalable.

### 7-Port FTTO Switch with two SFP uplinks and 54V DC powered

- 3 Uplink Ports (2x SFP and 1x RJ45)
- Power over Ethernet (PoE+), up to 150W
- Efficient Energy Management
- Memory Card Slot
- Input voltage range 46 ... 57V DC



## 7-Port FTTO Switch with one SFP uplink and 54V DC powered

- 3 Uplink Ports (1x SFP and 2x RJ45)
- Powered Device remote powering via Power over Ethernet
- Power over Ethernet (PoE+), up to 150Watts
- Efficient Energy Management
- Memory Card Slot
- Input Voltage Range 46 ... 57V DC



Reference	Description		
88303990	GigaSwitch V5 2TP(PSE+) SFP-VI 54VDC		
	User Ports (RJ45):	4x 1000Base-T	
	Uplink Ports (SFP):	1x 1000Mbps	
	Uplink Ports (RJ45):	2x 1000Base-T	
	No of PoE User Ports:	4x PSE(PoE+)	
	No of PoE Uplink Ports:	2x PSE(PoE+)	
88303991	GigaSwitch V5 2TP(PD-I	F+) SFP-VI 54VDC	
	User Ports (RJ45):	4x 1000Base-T	
	Uplink Ports (SFP):	1x 100/1000Mbps	
	Uplink Ports (RJ45):	2x 1000Base-T	
	No of PoE User Ports:	4x PSE(PoE+)	
	No of PoE Uplink Ports:	1x PD, 1x PSE (PoE+)	
88303992	GigaSwitch V5 2TP SFP-VI 54VDC		
	User Ports (RJ45):	4x 1000Base-T	
	Uplink Ports (SFP):	1x 1000Mbps	
	Uplink Ports (RJ45):	2x 1000Base-T	
	No of PoE User Ports:	4x PSE(PoE+)	
	No of PoE Uplink Ports:	<del>-</del>	

# **Product overview**

#### 6-Port FTTO Switch with one or two SFP uplinks and 230V AC powered

- 2 Uplink Ports (1x SFP and 1x RJ45 or 2x SFP)Efficient Energy Management
- Memory Card Slot
- Wide input voltage range 85 ... 240V AC



Reference	Description	
88303975	GigaSwitch V5 TP SFP-V	/I 230VAC
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 1x 1000Mbps 1x 1000Base-T -
88303971	GigaSwitch V5 SFP-2VI	230VAC
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps - -

## **7-Port FTTO Switch with** two SFP uplinks and 54V DC powered, Medical series

- 3 Uplink Ports (2x SFP and 1x RJ45)
- 4 Isolated User Ports (4kV and 2MOPP)
- Efficient Energy Management
- Memory Card Slot
- Input Voltage Range 46 ... 57V DC



Reference	Description	
88303611	GigaSwitch V5 TP(PSE+)	SFP-2VI 54VDC MED
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps 1x 1000Base-T - 1x PSE(PoE+)
88303612	GigaSwitch V5 TP SFP-2VI 54VDC MED	
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps 1x 1000Base-T -

## 6-Port FTTO Switch with one or two SFP uplinks and 230V AC powered,

### **Medical series**

- 2 Uplink Ports (2x SFP or 1x SFP and 1x RJ45)
- 4 Isolated User Ports (4kV and 2MOPP)
- Efficient Energy Management Memory Card Slot
- Input Voltage Range 85 ... 240V AC



Reference	Description		
88303658	GigaSwitch V5 TP SFP-VI 230VAC MED		
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 1x 1000Mbps 1x 1000Base-T	
88303603	GigaSwitch V5 SFP-2VI 230VAC MED		
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps -	

# **Product overview**

## **7-Port FTTO Switch with** two SFP uplinks and 54V DC powered, Industrial series

- 3 Uplink Ports (2x SFP and 1x RJ45)
- Robust Metal Housing and Compact Hardware Design
- Efficient Energy Management
- Memory Card Slot
- Input voltage range 46 ... 57V DC
  -25 ... +60°C



Reference	Description			
88303960	GigaSwitch V5 TP(PSE+) SFP-2VI 54VDC IND			
88313960	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps 1x 1000Base-T 4x PSE(PoE+) 1x PSE(PoE+)		
88303965	GigaSwitch V5 TP SFP-2VI 54VDC IND			
88313961	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 2x 1000Mbps 1x 1000Base-T 4x PSE(PoE+)		

## **7-Port FTTO Switch with** one SFP uplink and 230V AC powered, Industrial series

- 2 Uplink Ports (1x SFP and 1x RJ45)
- Robust Metal Housing and Compact Hardware Design
- Efficient Energy Management
- Memory Card Slot
- Wide input voltage range 85 ... 240V AC
- -25 ... +60°C



Reference	Description	
88303963	GigaSwitch V5 TP SFP-VI 230VAC IND	
	User Ports (RJ45): Uplink Ports (SFP): Uplink Ports (RJ45): No of PoE User Ports: No of PoE Uplink Ports:	4x 1000Base-T 1x 100/1000Mbps 1x 1000Base-T

#### Click-In Power Supply 54VDC/70W

- Easy and toolless installation
- Support of 45mm installation format
- Fanless System with aluminium faceplate for best thermal performance
- Output Power: 70 Watts
- Redundant connection without external diodes possible



Reference	Description	
88646210	Click-In Power Supply 54	VDC/70W 90x45
	Input range: Rated output range: Max. output power: Dimensions: Operating temp. range:	90-265V AC 54V DC 70W 90 x 45 x 46mm 0 45°C

## Click-In Power Supply 54VDC/130W

- Easy and toolless installation
- Support of 45mm installation format
- Fanless System with aluminium faceplate for best thermal performance
- Output Power: 130 Watts
- Redundant connection without external diodes possible



Reference	Description	
88646241	Click-In Power Supply 54VDC/130W 135x45	
	Input range: Rated output range: Max. output power: Dimensions: Operating temp. range:	90-265V AC 54V DC 130W 135 x 45 x 52mm 0 45°C

# **Product overview**

# Installation Power Supplies 54VDC/65W

- with pre assembled 3-pin connector or moulded 3-pin connector
- Fanless design
- Control-LED
- Output Power: 65 Watts



Reference	Description	
88646066	Installation Power Suppl	y 54VDC/65W
	Input range: Rated output range: Max. output power: Dimensions: Operating temp. range:	100-240V AC 54V DC 64,8W 120 x 54 x 32mm 0 40°C
88646077	Power Supply with Schuk	co 54VDC/65W
	Input range: Rated output range: Max. output power: Dimensions: Operating temp. range	100-240V AC 54V DC 64,8W 120 x 54 x 32mm 0 40°C

## **LANactive Manager**

- Stand-Alone version and Client-Controller version
- Zero-Touch Configuration
- Extended management for firmware and configuration changes
- Different access levels, roles and user specified device lists
- Logging and alarming functionality
- Free of charge evaluation version



Reference	Description
88301908	LANactive Manager Single User Licence
88301909	LANactive Manager Company Licence
88301920	LANactive Manager Controller Licence

## **Memory Cards**

- Own MAC Address
- Backup of latest firmware and configuration
- Easy exchange of a failed switch
- Extended temperature range: -40...85°C



Reference	Description
88300691	microSD Card with MAC Delivery: Separately in plastic case
88300693	microSD Card with MAC, integrated Delivery: Pre-installed in the switch

## **USB Console Cable GigaSwitch Series**

- USB to 10-Pin mini-socket console cable
- On-site configuration of Aginode GigaSwitch Series
- Same functionality as configuration via Telnet or SSH
- Easy connection via USB



Reference	Description
88300715	USB Console Cable GigaSwitch Series Connector A: 10-pin mini-socket Connector B: USB

# **Product overview**

## **Aginode SFP 1000** Transceiver GI(LC)

- Gigabit EthernetDigital Diagnostic Monitoring
- Wide Temperature Range (-40°C up to +85°C)
- LC connector



Reference	Description		
88646015	Aginode SFP 1000 Transceiver GI(LC)E		
	Data rate: Fiber Type: Link Type: TX Wavelength: RX Wavelength: Link Length:	Gigabit Eth. multi mode dual fiber 850nm 850nm 550m	
88646016	Aginode SFP 1000 Transceiver SM(LC)E L10		
	Data rate: Fiber Type: Link Type: TX Wavelength: RX Wavelength: Link Length:	Gigabit Eth. single mode dual fiber 1.310nm 1.310nm	

## Aginode SFP 1000 Transceiver SM(LC) BIDI

- Gigabit EthernetDigital Diagnostic Monitoring
- Wide Temperature Range (-40°C up to +85°C)
- LC connector



Reference	Description		
88646073	Aginode SFP 1000 Transceiver SF3(LC)E L10		
	Data rate: Fiber Type: Link Type: TX Wavelength: RX Wavelength: Link Length:	Gigabit Eth. single mode single fiber 1.310nm 1.550nm	
88646075	Aginode SFP 1000 Tr Data rate: Fiber Type: Link Type: TX Wavelength: RX Wavelength: Link Length:	ansceiver SF5(LC)E L10  Gigabit Eth. single mode single fibre 1.550nm 1.310nm 10km	

#### Cover set 45x90


- Universal mounting frame
- Wide range of compatibility
- Pure white, like RAL 9010
- Integrated locking mechanism



Reference	Description
88646030	Cover set 45x90 incl. MF, PW/9010 80x150

## **Legrand Cover Set 45x90**

- 45x90mm or 45x135mm
- 45mm Snap-In mechanism
- Signal white, like RAL 9003



Reference	Description
88646031	Cover 82x153/45x90 LGD, SWS, hor
88646032	Universal mounting frame for LGD 82x153
88646266	Cover 82x224/45x135 Legrand, white, hor.
88646267	Universal support for Legrand cover 82x224

## Installation profile 4x6 Click-In

- Suitable for GigaSwitch and Click-In 70W or 130W power supplies
- Incl. wall mounting kit
- 4x M25 holes for cable glands
- Hole for Kensington lock
- Compact design



Reference	Description	
88646310	Installation profile 4x6	Click-In RAL 9010, 4xPG
	Dimensions (WxHxD): Material: Colour:	70 x 52 x 400 mm Painted sheet steel pure white, like RAL 9010
88646037	Blind cover 45x45, RAL 9010	
	Dimensions (WxHxD): Material: Colour:	45 x 45 mm Plastic pure white, like RAL 9010

# **Product overview**

#### Installation profile 4x6 Click-In

- Integration of 2 Switches

- 230VAC supply via power connector
  65W 54VDC power supply
  1x opening for Twisted Pair patch cord
- Dimensions (BxHxT): 56x56x500 mm



Reference	Description
88646189	Dual Version Profile 56x56x500 RAL9010, incl. PSU Wago
88646191	Mounting kit for cable tray systems
88646192	Mounting kit for wall mounting
88646196	DIN rail mounting kit

## Mounting Kit GSw 190x40x70mm

- Housing for mounting a LANactive FTTO switch
- Optimized for wall or desktop mounting
- Strain relief on the side
- 45x90mm slot for the FTTO switch



Reference	Description
88646299	Mounting Kit GSw 190x40x70mm

## **#smartconnection**



Contact us via info@aginode.net

April 2024, Aginode. All rights reserved. All details are indicative only and subject to change, All trademarks registered by Aginode. kd-1922e01